




Applicator Setup Form

Company: Gentherm Date: 3/9/18
 Contact: Jose Rosales p.c. 6289605
 Phone: +52(846)988-1041 Email: Jose.Rosales@gentherm.com
 Terminal Mfg. & Part # DigiCH 1206E214 (1206407A)

Wire Size: 1.5 sqmm (1200918A)
 Do you want Mecal crimp specs: YES NO If no, please provide your own using the area below.

WIRE	CCW	CCW	ICH	ICW
1.5 sqmm	1.85 +/- 0.03	3.00 +/- 0.05	3.20 +/- 0.05	3.70 +/- 0.05

Press must have a 135.8mm shut height.
 Press Stroke: 40mm 30mm Other: _____
 Carrier strip to be cut: No Yes
 Data Plate Units (Company Preference) inches: MM X _____
 Automatic Machine Bench Top Press _____
 Stripper Unit: None Mecal Other _____



Description of Machine or Press (ie: Komax / TT, G-press) Komax
 We will need 150 continuous terminals and 10 feet of each wire size to process and complete our testing.
 Note: Crimp Tool # 32099 103A

For Mecal Use Only

Customer: Mecal by Starn Serial no. _____ Order nr _____ Date _____
 Terminal manufacturer & related part number _____ Miniapplicator model _____ Qty: _____
 End feed Pneumatic Positive cam ("present" terminal)
 Left side feed Mechanical Negative cam ("absent" terminal)
 Seal to be Crimped: Yes _____ No _____ Ejector Style: Standard _____ 10MM _____ Both _____



30 m
 Wire 1.50sqmm

